



**HIGHLY SENSITIVE, LIGHTWEIGHT  
BACKPACK RADIATION DETECTOR (BRD)**

# FLIR identiFINDER® R700



The FLIR identiFINDER R700 Backpack Radiation Detector (BRD) offers a hands-free capability for broad-area radiological search and monitoring missions. The identiFINDER R700 provides the user all that is required to successfully perform wide-area searches quickly, efficiently and confidently. Providing the ultimate versatility, the identiFINDER R700 can be placed for stationary monitoring at makeshift checkpoints, fence-line monitoring, and other temporary screening locations. When coupled with radiation monitoring software, the identiFINDER R700 can be used as a fixed-site monitoring tool.

[flir.com/r700](http://flir.com/r700)



## INTERROGATE AND ISOLATE RADIOLOGICAL THREATS QUICKLY

Building on the award-winning identiFINDER R440, the R700 offers an advanced spectroscopic algorithm and detection techniques scaled up to a man-portable backpack for increased sensitivity and speed


- Detect harmful neutrons with NaI or count them with our dual-mode NaI detector without the need for an additional neutron detector
- Large 2" x 4" x 8" detector allows for rapid detection and identification of even the smallest radiation sources; source-less "quantum gain" stabilization improves data collection, reducing false positives
- 360° EasyFinder™ mode collects and interprets data to pinpoint radiation at the source, enabling faster location of threats



## DEPLOY AT THE SCENE OR ON THE MOVE, COVERTLY

The R700's capabilities configured as a backpack or a stationary device allow multiple mission sets from wide area searches to temporary check points

- Ergonomic design for all day operator wear- the long battery life and balanced load are designed for extended missions
- Unmarked backpack form-factor and mobile phone-based user interface allow operators to detect radiological threats covertly, even in a crowd
- Included tripod mount enables stationary deployment for remote radiation monitoring. The rugged and weatherproof IP67 design operates in the harshest weather conditions



## SHARE INTELLIGENCE BROADLY, OR OPERATE SILENTLY

Providing critical information to decision makers quickly is essential. The R700 provides the capability to do so in real-time and on demand

- Ability to monitor and control remotely using the Mobile App (iOS (available), Android (future))
- Built-in wireless communications and a robust API enable integration with user-deployed networks. ANSI N42.42 data output is standard for easy integration
- Tethered-display versions will provide a radio silent (air-gapped) option for highly sensitive missions

## SPECIFICATIONS

System Overview	
Technology	Backpack Radiation Detector (BRD)
Threats	Detects gamma and/or neutron radiation emitted from natural occurrences in the environment, special nuclear material, industrial, or medical material
Technology	
Detector	2 x 4 x 8" NaI™ (NaI:Tl, Li) gamma-neutron or 2 x 4 x 8" NaI(Tl) gamma-neutron indication
Typical Resolution	≤8.5% FWHM at 662 keV (20 °C)
Stabilization	Sourceless "Quantum gain" stabilization (patents pending)
Energy Range [Gamma]	10 keV to 10 MeV (All detectors)
Dose rate range (Cs-137)	0.001 mrem/h - 10 rem/h (0.01 - 100,000 μSv/h)
Dose rate range ID mode (Cs-137)	0.001 - 0.5 mrem/h (0.01 - 5 μSv/h)
Dose rate overload range (Cs-137)	0.002 - 10 rem/h (20 - 100,000 μSv/h)
Gamma Sensativity (Cs-137)	165,000 cps/mrem/h (16,500 cps/uSv/h)
Neutron Sensativity	90 cps/nv
Linearization	Real-time linearization of gamma energy
Service Interval	5 year factory maintenance recommended, not required
Standards Compliance	ANSI N42.53 BRD standard fully compliant ANSI N42.42 data format fully compliant IEC 62694 backpack standard fully compliance IEC 62706 BRD environmental compliant IEC 62755 data format fully compliant
Sampling & Analysis	
Library Categories	SNM, SNMR, IND, MED, NUC, NORM, UKN
Nuclide Identification	Exceeds ANSI N42.53
Sample Introduction	Absorption of EM gamma (NaI) or gamma and neutron emissions (NaI/L)
Time to Alarm	From a few seconds to minutes
Time to ID	Depends on gamma exposure; typically < 2 min

Environmental	
Operating Temperature	-4 to 122 °F (-20 to 50 °C)
Operating Humidity	10 to 100% non-condensing (IP67)
Storage Temperature	-4 to +104 °F (-20 to +40 °C )
Protection Rating	IP67 according to IEC 60529 (3' (1 m) submersible)
System Interface	
Communication	USB 2.0, USB OTG; Bluetooth® Class BLE 4.0 and 2.1 with EDR ≤30m range (can be disabled at manufacture)
Data Storage	32GB internal memory
GPS (removable)	72-channel u-blox M8 engine
Software	On-board web server software
Training Requirements	<10 mins for operator; 1 day for advanced user
Power	
Battery Specs	2x rechargeable Li-Ion smartpacks (hot-swappable)h runtime per Li-Ion smartpack; > 9 h runtime with single battery pack > 18 h runtime with dual batteries
Input Voltage	100-240V AC (wall adapter and USB cable supplied)
Cold Start Time	<5 mins from cold start
Physical Features	
Enclosure and Protection	Impact resistant plastic; protection rating IP67 according to IEC 60529
Dimensions [L x W x H]	≤17 x 12 x 20 in (≤43.2 x 30.5 x 50.8 cm)
Weight	≤22 lbs (≤10 kg)



For a complete list of specifications, go to [flir.com/r700](http://flir.com/r700)

**CORPORATE HEADQUARTERS**  
FLIR Systems, Inc.  
1201 S. Joyce Street  
Suite C006  
Arlington, VA 22202  
PH: +1 703.682.3400

**DETECTION SALES, EMEA**  
FLIR Detection, Inc.  
Luxemburgstraat 2  
2321 Meer  
Belgium  
PH: +32 (0) 3665 5106

**DETECTION SALES, APAC**  
FLIR Detection, Inc.  
10 Kallang Avenue #09-10  
Aperia Tower 2  
Singapore 335910  
PH: +65-6822-1596

[www.flir.com](http://www.flir.com)  
NASDAQ: FLIR

Equipment described herein is subject to US export regulations and may require a license prior to export. Diversion contrary to US law is prohibited. Imagery for illustration purposes only. Specifications are subject to change without notice. ©2021 FLIR Systems, Inc. All rights reserved. Created: 04/27/2021

21-0335-DET-identiFINDER R700 Datasheet - A4



The World's Sixth Sense®

**RMI, s.r.o.**  
Pernštýnská 116  
533 41 Lázně Bohdaneč  
Tel: 466 921 885, 404  
e-mail: [sale@rmi.cz](mailto:sale@rmi.cz)  
web: [www.rmi.cz](http://www.rmi.cz)