

Precise Focusing Stage



Accessory can be combined with all models of miniRaman spectrometer

- Provides protection from ambient light
- Provides a safe operation since user will not see the laser irradiation
- Provides precise focusing of the laser beam on a sample

Precise Focusing Stage XYZ



- lateral travel range: 25 mm along the X and Y axes
- axial travel range: 25 mm
- precise focusing of the laser beam on a sample in axial and lateral dimensions with accuracy 10 μm
- magnetic fixation of the stage cover in up and down positions
- weight: 3,2 kg
- dimensions: 215 mm x 175 mm x 320,5 mm

Precise Focusing Stage Z



- axial travel range: 25 mm
- precise focusing of the laser beam on a sample in axial dimension with accuracy 10 μm
- magnetic fixation of the stage cover in up and down positions
- weight: 2,5 kg
- dimensions: 215 mm x 175 mm x 320,5 mm

 **Lightnovo**

RMI, s.r.o.
Pernštýnská 116
533 41 Lázně Bohdaneč
Tel: 466 921 885, 404
e-mail: sale@rmi.cz
web: www.rmi.cz

Lightnovo ApS
Blokken 15, 1. tv.
3460 Birkerød
Denmark (DK)
CVR: 40979603

+45 71 37 04 10
info@lightnovo.com
<https://lightnovo.com>

