

IDENTIFINDER® R425

Next Generation Radionuclide Identification Device



The identiFINDER R425, the next generation of the most deployed radionuclide identification device (RID), offers 360-degree coverage so you can locate and measure gamma and neutron radioactive sources built with Teledyne FLIR's trusted algorithms with advanced heuristics and hybrid identification techniques.

The newest and latest updates to the R425 feature a new glass screen cover to boost its ruggedness, an increase of the GM tube to 1000 R/h adding a higher dose capability, and an LaBr detector offering higher resolution option providing a better energy resolution capability.

Operate the R425 quickly with the familiar identiFINDER user interface and 3-button control. When other systems fail in extremely high gamma fields, the identiFINDER R425 provides pinpoint accuracy and remains fully operational. The R425 provides an ideal balance of size, weight, and performance for surveying, emergency response, and environmental monitoring.



www.flir.com/r425

BETTER DETECTION IN ALL DIRECTIONS

With over 25,000 deployed RIDs, the R425 builds on a solid legacy of performance in every way

- Threats come from every direction. The cubic detector design allows for high performance in all directions.
- Greater sensitivity with 75% larger detector, and 2X Neutron sensitivity.
- 15% lighter weight than the previous generation.
- The LaBr detector option will provide $\leq 3.5\%$ resolution.

POWER THROUGH YOUR MISSION

Unparalleled ruggedness, power flexibility, and usability means the R425 will go the distance and complete the mission with you.

- Drop on the ground, submerge it in water. It will survive. Fully enclosed solid-state detector. Ergonomic design and rubberized grip.
- Sunlight readable screen, even with polarized glasses. Internal battery lasts up to 12 hours. Need more? Hot swappable batteries (rechargeable AND disposables) add 2 hours of use. Ready in 15 seconds or less from a cold start.
- Same tried and trusted interface as the R400. Pick it up and go.



SITUATIONAL AWARENESS WHEN YOU NEED IT

When threat detection occurs, getting results communicated as quickly as possible is critical. R425 makes it easier than ever before, no matter the method.

- Remote viewing, operation, and reachback over Bluetooth via available app (iOS/Android) or over USB-C via FLIR's intuitive Web Interface.
- Universal API to enable integration with user deployed networks such as Mobile Field Kit, ATAC, Sigma Edge, Safe Environment Gateway, and others.
- Wi-Fi and Cellular connectivity via optional adapter.

SPECIFICATIONS

identiFINDER R425		Power	
Technology	Radionuclide identification device (RID); Gamma and Gamma/Neutron Models	Input Voltage	100-240 AC (wall adapter and USB-C cable supplied)
Gamma Detector - NaI (TI) (G & NG Models)	1.77 x 1.77 x 1.77 in (45 x 45 x 45 mm) cubic detector with silicon photomultiplier (SiPM)	Battery Specification	Internal Li-ion cells; additional user-selectable external battery (1 each 16650 Li-ion or 2 each CR123); hot-swappable
Gamma Detector - LaBr3(Ce) (LG & LNG Models)	1.4 x 1.4 x 1.4 in (35 x 35 x 35 mm) cubic detector with silicon photomultiplier (SiPM)	Cold Start Time	≤20 seconds from cold start
High Dose Rate Gamma Detector	Energy Compensated Geiger Müller (GM) Tube	Environmental	
Neutron Detector - ZnS (GN & LGN models only)	27 x 58 x 5 mm moderated panels (2 each)	Operating Temp	-22 to 140 °F (-30 to 60 °C)
Energy Range (Gamma)	20 keV - 3 MeV	Operating Humidity	10 to 93%, non-condensing
Gamma Sensitivity (Cs-137)	1610 cps/uSv/h (G & GN models) 1000 cps/uSv/h (LG & LGN models)	Storage Temperature	14 to 95 °F (-10 to 35 °C)
Neutron Sensitivity	> 4 cps/nv	Physical Features	
Gamma Spectrum Length	1024 channels	Dimensions (L x W x H)	9.3 x 3.9 x 3.7 in (235 x 100 x 95 mm)
Dose Rate Range (Cs-137)	10 µrem/h – 1 rem/h ± 10%, 100 nSv/h – 10 mSv/h ± 10%	Weight	≤2.6 lbs (≤1.2 kg)
Dose Rate Range ID Mode (Cs-137)	0.1 µrem/h – 5 mrem/h 1 nSv/h – 50 µSv/h	Enclosure & Protection	Injection molded housing with overmold; rating IP67 according to IEC 60529; MIL-STD 810g Salt / Fog compliant
Overload Dose Rate Range	1 - 1000 rem/h 10 mSv/h - 10 Sv/h		
Stabilization	Sourceless gain stabilization		
Linearization	Real time linearization of gamma energy		
Typical Resolution	≤ 7% FWHM at 662 keV (20°C) (G&GN models) ≤ 3.5% FWHM at 662 keV (20°C) (L&LN models)		
Service Interval	5-year factory maintenance		
Sampling & Analysis			
Sample Introduction	Absorption of EM gamma and neutron emissions		
Threats	Detects neutron and gamma radiation emitted from natural occurrences in the environment, special nuclear material, industrial, or medical material		
Nuclide Identification	According to ANSI N42.34		
Library Categories	SNM, IND, MED, NORM		
Time to Identification	From a few seconds to a few minutes		
System Interface			
Display & Alerts	2.7" diagonal (400x240 pixels) screen; sunlight readable; visible through polarized glasses		
Communications	USB-C (2x), Bluetooth (BLE 5.0)		
Data Storage	8GB internal memory		
Training Requirements	<10 mins for operator; 1 hour for advanced user		
Software	Onboard webserver software		
Data File Format	According to ANSI N42.42		



Specifications are subject to change without notice.
For the most up-to-date specs, go to www.teledyneflir.com

AMERICAS

7055 Troy Hill Dr. Suite 300
Elkridge, MD 21075 USA

APAC

10 Kallang Avenue #09-10
Aperia Tower 2
Singapore 335910

EMEA

Luxemburgstraat 2
2321 Meer
Belgium

RMI, s.r.o.
Pernštýnská 116
533 41 Lázně Bohdaneč
Tel: 466 921 885, 404
e-mail: sale@rmi.cz
web: www.rmi.cz

This product is subject to United States export regulations and may require US authorization prior to export, reexport, or transfer to non-US persons or parties. Diversion contrary to US law is prohibited. For assistance with confirming the Jurisdiction & Classification of Teledyne FLIR, LLC products, please contact exportquestions@flir.com. ©2023 Teledyne FLIR LLC. All rights reserved.

Revised on 04/04/23
identiFINDER R425_Datasheet-A4 23-0323